

Specifications

	Model Name	CL-S200BF : Protective Filter CL-S200BN : No Protective Filter	CL-S300BF : Protective Filter CL-S300BN : No Protective Filter
LCD Panel	Technology	21.3" color TFT IPS technology	21.3" color TFT IPS technology
	Display Area	324 mm × 432 mm	324.86 mm × 433.15 mm
	Pixel Pitch	0.270 mm × 0.270 mm	0.2115 mm × 0.2115 mm
	Contrast Ratio	1800 : 1 (typ.)	1500 : 1 (typ.)
	Maximum Luminance	1000 cd/m² (typ.) 410 cd/m² / 500 cd/m² (calibrated)	1000 cd/m² (typ.) 410 cd/m² / 500 cd/m² (calibrated)
	Viewing Angle	178° vertical and horizontal	178° vertical and horizontal
Visual Performance	Native Resolution	1200 × 1600	1536 × 2048
	Display Colors	16.77 million colors from a palette of 68 billion colors 1.07 billion colors with DisplayPort and 10-bit viewer	16.77 million colors from a palette of 68 billion colors 1.07 billion colors with DisplayPort and 10-bit viewer
Interface	Input Signal	DVI-D (DVI 1.0 compliant) DisplayPort (DisplayPort 1.2a compliant)	DVI-D (DVI 1.0 compliant) DisplayPort (DisplayPort 1.2a compliant)
	Output Signal	DisplayPort (DisplayPort 1.2a compliant)	DisplayPort (DisplayPort 1.2a compliant)
	Plug and Play	DDC2B compliant	DDC2B compliant
Input Power Supply	Input Power Supply	100 V - 240 V 50 / 60Hz	100 V - 240 V 50 / 60Hz
	Maximum Power Consumption	65 W (typ.)	95 W (typ.)
Features	Calibration Control	Luminance, Gamma, Color temperature Capable of storing 3 sets of LUT (Optional Calibration Kit is required)	Luminance, Gamma, Color temperature Capable of storing 3 sets of LUT (Optional Calibration Kit is required)
	OSD Information Display	Model name, Serial No., Total operating time, Calibration settings (Operating time since last calibration, Luminance, Gamma), Current luminance, Color temperature and Ambient light, DICOM conformance	Model name, Serial No., Total operating time, Calibration settings (Operating time since last calibration, Luminance, Gamma), Current luminance, Color temperature and Ambient light, DICOM conformance
	USB Hub	USB Rev.2.0 compliant, Self-powered USB upstream connector (x1), USB downstream connector (x2)	USB Rev.2.0 compliant, Self-powered USB upstream connector (x1), USB downstream connector (x2)
	Other Features	Uniformity Equalizer, Hardware pivot, LED indicator, Advanced power management, Human Presence Sensor, Dynamic Gamma, Auto Text Mode, Luminance stabilization, Multiple LUT, Self DICOM check, Self-calibration	Uniformity Equalizer, Hardware pivot, LED indicator, Advanced power management, Human Presence Sensor, Dynamic Gamma, Auto Text Mode, Luminance stabilization, Multiple LUT, Self DICOM check, Self-calibration
	Approvals	ANSI/AAMI ES60601-1 (2005) + A1 (2012), CAN/CSA-C22.2 No. 60601-1 (2014), CE (EN60601-1, EN60601-1-2), RCM, FCC Part15 subpart B Class B , ICES-003-B, VCCI-B, FDA510(k), J-Moss, RoHS	ANSI/AAMI ES60601-1 (2005) + A1 (2012), CAN/CSA-C22.2 No. 60601-1 (2014), CE (EN60601-1, EN60601-1-2), RCM, FCC Part15 subpart B Class B , ICES-003-B, VCCI-B, FDA510(k), J-Moss, RoHS
Physical Characteristics	Dimensions (W × H × D)	Landscape : 493 mm × 451.3 / 546.3 mm × 196.5 mm Portrait : 361.5 mm × 517 / 612 mm × 196.5 mm	Landscape : 493 mm × 451.3 / 546.3 mm × 196.5 mm Portrait : 361.5 mm × 517 / 612 mm × 196.5 mm
	Weight	approx. 9 kg	approx. 10 kg
	Tilt Stand	Tilt, Swivel, Portrait / Landscape	Tilt, Swivel, Portrait / Landscape
	Mount	VESA standard (100 mm × 100 mm)	VESA standard (100 mm × 100 mm)
	Security Slot	Anti-theft security slot	Anti-theft security slot
	Accessories	Power cord, DisplayPort cable, USB cable, Operation manual, Installation manual, Software (QA Medivisor Agent LE)	Power cord, DisplayPort cable, USB cable, Operation manual, Installation manual, Software (QA Medivisor Agent LE)

Dimensions (mm)



Interface





• "JVC" is a brand of medical and industrial monitors manufactured and sold by JVCKENWOOD Corporation. • Company names and product names are the registered trademarks of the respective companies. • Product specifications and appearance are subject to change without notice. • Colors in photographs may differ from actual colors due to the printing process. •Images on screens are simulated.



Please read the user's manual for safe and proper use.

 Do not expose the product to dust, moisture, steam, or oily smoke. It could cause fire, electric shock, or a failure.

Healthcare Business Division JVCKENWOOD Corporation

3-12, Moriya-cho, Kanagawa-ku, Yokohama-shi, Kanagawa, 221-0022, JAPAN TEL: +81-45-450-1908 FAX: +81-45-450-1926

Email: MEDICAL-DISPLAY.J_JKC@jvckenwood.com JVC Healthcare Website : http://healthcare.jvc.com/ Please contact our distributor below with inquiries and orders.



2 Megapixel 21.3" Color Monitor


CL-S200

3 Megapixel 21.3" Color Monitor

CL-S300

Unparalleled Innovation in Diagnostic Imaging





for Medical Imaging SERIES





















Providing the Best Diagnostic Environment Fully redesigned hardware and software bring

Fully redesigned hardware and software bring innovation in multi-modality image reading.

■ Clearly Defined Diagnostic Images

ensures that the monitor constantly performs at its best.


The new i3 color series render more precise color and monochrome modality

images. One of its unique technologies the built-in self-calibrating sensor

Pursuing an Effective Diagnostic Reading Environment

Dynamic Gamma

Color Images are automatically recognized to provide optimized contrast, brightness and gamma. No user intervention is required.



Auto Text Mode

Brightness is automatically adjusted on patient lists and reporting applications to reduce eye strain.







Indicator

Auto Text Mode OFF Auto Text Mode ON

Integrated QA Solution QA Medivisor Agent (Option)

Quality Assurance Made Easy and Cost Effective

QA Medivisor Agent providing calibration and QA standard testing capabilities through an intuitive and easy to navigate user interface makes it effective to manage day-to-day operation in the radiology department. Simplified calibration scheduling tool QA Medivisor Agent LE is included.





*Optional calibration kit CAL-016 is required for standard QA testing.

| Self-calibration

With the integrated color front sensor, the CL-S200 / CL-S300 self-calibrates to the DICOM Part 14 Standard on a regular schedule.



Schedule Setting (QA Medivisor Agent)

Razor-sharp Color Precision

Utilizing its unique X, Y, Z, color level tracking and color management technologies, any of the i3 model perfectly color-matches one another.



for Medical Imaging SERIES

Without Calibration

Advanced Features

- Premium Design
- LED Indicator / Front Buttons
- Built-in Sensor
- Space Saving
- Two-tone Color
- Wire Management / DisplayPort Daisy Chains

Premium Design

A simple and slim design for a

DICOM Calibration




LED Indicator / Front Buttons

The soft LED light indicator and front buttons are streamlined for intuitive operation.



Built-in Sensor



ation and

Automatically switching to power save mode when sensor does not detect human presence.

Human Presence Sensor

Space Saving

The new design of the CL-S200 / CL-S300 reduces 25% of the stand footprint compared to the conventional models.



Two-tone Color

The back side features a stylish gray-white tone color.

Wire Management / DisplayPort Daisy Chains

With the DisplayPort 1.2, the use of daisy chains allows for easier wiring connections.



Optional graphic card is required for daisy chains connections.